

ORDER FORM BATEC RAPID 2 PLUS RANGE

Dealer: _____ Address: _____
 City: _____ User Name: _____
 P.O.Number: _____ Date: _____

PARA MODELS

BATEC RAPID 2 PLUS
 _____ \$

- B25.31.001 | Graphite with red details
- B25.31.010 | Graphite with red details limited to 6 Km/h |
- B25.31.014 | Graphite with red details limited to 10 Km/h |
- B25.31.018 | Graphite with red details limited to 15 Km/h |



QUAD MODELS

BATEC QUAD RAPID 2 PLUS
 _____ \$

- B25.31.004 | Graphite with red details
- B25.31.011 | Graphite with red details limited to 6 Km/h |
- B25.31.015 | Graphite with red details limited to 10 Km/h |
- B25.31.019 | Graphite with red details limited to 15 Km/h |



HEMI MODELS

BATEC HEMI RAPID 2 PLUS
 _____ \$

- | | |
|----------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------|
| <input type="checkbox"/> B25.31.007 Graphite with red details Hemi Right | <input type="checkbox"/> B25.31.008 Graphite with red details Hemi Left |
| <input type="checkbox"/> B25.31.012 Graphite with red details Hemi Right limited to 6Km/h | <input type="checkbox"/> B25.31.013 Graphite with red details Hemi Left limited to 6 km/h |
| <input type="checkbox"/> B25.31.016 Graphite with red details Hemi Right limited to 10Km/h | <input type="checkbox"/> B25.31.017 Graphite with red details Hemi Left limited to 10 Km/h |
| <input type="checkbox"/> B25.31.020 Graphite with red details Hemi Right limited to 15Km/h | <input type="checkbox"/> B25.31.021 Graphite with red details Hemi Left limited to 15 km/h |



All Batecs include charger and Batec Docking Bar.



NOTE: We would like to point out that the versions of the device which drive faster than 6 kph are only permitted in road traffic in certain countries and otherwise may only be used on private land. In the absence of approval, in accordance with the road traffic laws, the versions which drive faster than 6 kph version may not be driven on public roads or even cycle ways. It is your responsibility to find out the information about which legal regulations apply in your particular country and about the insurance or driving licence obligations for versions which drive faster than 6 km/h.

OPTIONS - BATEC 4 ALL

HANDLEBAR PARA*



- Twist throttle left hand B27.01.005 _____ \$
- Thumb throttle right hand B27.01.003 _____ \$
- Thumb throttle left hand B27.01.004 _____ \$
- Double brake lever right hand derecha | B27.01.008 _____ \$
- Double brake lever left hand izquierda | B27.01.009 _____ \$
- 4 Buttons pad right hand B27.01.010 _____ \$
- 4 Buttons pad left hand B27.01.011 _____ \$

* Batec handlebars are supplied as standard with right-hand throttle and two brake levers.

HANDLEBAR QUAD



For customisation of the tetra handlebars, please contact us.

HANDLEBAR HEMI



- Twist throttle right hand B27.04.001 _____ \$
- Twist throttle left hand B27.04.002 _____ \$

BATEC FOR TALL Not compatible with quad models.

- Extra-tall handlebar BATEC FOR TALL (includes: taller handlebar, control- button extenders, twist-throttle extender, longer brake cables and covers). | B27.01.007 _____ \$



OPTIONS - OTHERS

Optional suspension stand frame

_____ \$

- B27.02.001



Standard on the BATEC SCRAMBLER. Optional on the rest of the line.

BATEC RINGS

_____ \$

- B27.02.002



BATTERY AND ACCESORIES

- 48 V-768 Wh (16 Ah) lithium battery | B26.01.012

_____ \$



- Transformer for the car 12V/230V | B54.03.13

_____ \$

ACCESSORIES

BATEC EXCURSION 2 front rucksack

_____ \$

B54.05.10



Includes
BATEC PORTA
luggage rack

BATEC BOSSA rucksack

_____ \$

B54.05.01



BATEC CINCHA Hooks for a crane

_____ \$

B54.05.06



BATEC 4KG Weight

_____ \$

B54.05.05



BATEC RODES

Off-road wheels

_____ \$

B54.04.03



BATEC AXLES & SPACERS
included for free



All BATEC RODES are supplied as a standard with aluminium handrims.
Ask us for vinyl handrims under request.

BATEC WHEELS BAG

for 24" and 25" wheels

_____ \$

B54.05.03



BRACKETS

	D1 PV3 - Flat V shape brackets for fixed frame	<input type="checkbox"/>	B53.01.10	_____ \$
	D1 CNC - Machined brackets for folding frame	<input type="checkbox"/>	B53.01.11	_____ \$
	D1 PS3 - PANTHERA BRACKETS for Short frame	<input type="checkbox"/>	B53.01.50	_____ \$
	D1 PL3 - PANTHERA BRACKETS for Long frame	<input type="checkbox"/>	B53.01.51	_____ \$

BRAKES

	D3 NR - Standard Brakes push-to-lock mounted on Batec clamps	<input type="checkbox"/>	B53.03.10	_____ \$
	D3 NT - Composite Scissor Brakes mounted on Batec clamps	<input type="checkbox"/>	B53.03.12	_____ \$

STANDARD CLAMPS

	D2 N19 - Round tube wheelchair clamps Ø19mm	<input type="checkbox"/>	B53.02.40	_____ \$
	D2 N22 - Round tube wheelchair clamps Ø22mm	<input type="checkbox"/>	B53.02.41	_____ \$
	D2 N25 - Round tube wheelchair clamps Ø25mm	<input type="checkbox"/>	B53.02.42	_____ \$
	D2 N28.8 - Round tube wheelchair clamps Ø28.8mm	<input type="checkbox"/>	B53.02.43	_____ \$
	D2 N30 - Round tube wheelchair clamps Ø30mm	<input type="checkbox"/>	B53.02.44	_____ \$
	D2 N31.6 - Round tube wheelchair clamps Ø31.6mm	<input type="checkbox"/>	B53.02.45	_____ \$
	D2 N35 - Round tube wheelchair clamps Ø35mm	<input type="checkbox"/>	B53.02.46	_____ \$
	D2 NH - QUICKIE oval tube wheelchair clamps (for HELIUM & XENON)	<input type="checkbox"/>	B53.02.47	_____ \$
	D2 NJ - PROGEO JOKER oval tube wheelchair clamps	<input type="checkbox"/>	B53.02.48	_____ \$
	D2 NT - PROGEO TEKNA / NOIR oval tube wheelchair clamps	<input type="checkbox"/>	B53.02.49	_____ \$

	D2 NC - CYCLONE XLR oval tube wheelchair clamps	<input type="checkbox"/>	B53.02.50	_____ \$
	D2 NB - OTTOBOCK BLIZZARD oval tube wheelchair clamps	<input type="checkbox"/>	B53.02.51	_____ \$
	D2 NPR - TNS PROVAL oval tube wheelchair clamps	<input type="checkbox"/>	B53.02.52	_____ \$
	D2 N19-22 - PANTHERA- Round tube wheelchair clamps Ø19mm / Ø 20mm	<input type="checkbox"/>	B53.02.54	_____ \$
	D2 AVANG - Clamps for OTTOBOCK Avantgarde round tube wheelchairs	<input type="checkbox"/>	B53.02.55	_____ \$
	D2 MN30 - Clamps for MEYRA Nano Ø 30 mm round tube wheelchairs	<input type="checkbox"/>	B53.02.56	_____ \$
	D2 MP25 - Clamps for MEYRA Ø 25mm folding round tube wheelchairs	<input type="checkbox"/>	B53.02.57	_____ \$
	D2 KRIP - Oval tube clamps (QUICKIE KRIPTON)	<input type="checkbox"/>	B53.02.59	_____ \$
	D2 DUKE - Oval tube clamps (PROGEO DUKE/NOIR 2.0)	<input type="checkbox"/>	B53.02.60	_____ \$
	D2 MNX30 - Oval tube clamps Ø30mm (MEYRA Nano Nx)	<input type="checkbox"/>	B53.02.61	_____ \$

SPECIAL CLAMPS SETS

	D6 ADV - KUSCHALL ADVANCE CLAMPS SET (clamps + adaptor)	<input type="checkbox"/>	B53.06.01	_____ \$
	D6 ICO - ICON CLAMPS SET (clamps + adaptor)	<input type="checkbox"/>	B53.06.03	_____ \$
	D6 CS1 - CSEI CLAMPS SET (clamps + adaptor)	<input type="checkbox"/>	B53.06.04	_____ \$
	D6 CS2 - CSEI EVO CLAMPS SET (clamps + adaptor)	<input type="checkbox"/>	B53.06.05	_____ \$

ADAPTORS

	D5 PRO - Adaptors for Pro Activ wheelchairs	<input type="checkbox"/>	B53.05.03	_____ \$
	Adaptors for fixed frame w/ tapered seat	<input type="checkbox"/>	B53.05.04	_____ \$
	D5 PU - Adaptor for saving a seat bar for fixed frame	<input type="checkbox"/>	B53.05.06	_____ \$
	D5 BA - Adaptor for moving the clamps for folding frame	<input type="checkbox"/>	B53.05.07	_____ \$
	D5 ES - Set of spacers for fixed or folding frame wheelchairs or D5 50	<input type="checkbox"/>	B53.05.08	_____ \$
	D5 RE - Adaptor for moving the rear clamp backwards for fixed frame	<input type="checkbox"/>	B53.05.05	_____ \$
	D5 REC - Curve adaptor for moving the rear clamp backwards	<input type="checkbox"/>	B53.05.09	_____ \$
	D5 RE2 - Adaptor for moving backwards both clamps	<input type="checkbox"/>	B53.05.11	_____ \$
	D5 FK - Brake adapt short folding wheelch	<input type="checkbox"/>	B53.05.10	_____ \$


DETAILS OF WHEELCHAIR THE BATEC WILL BE INSTALLED ON

Brand	
Model	
Seat width	CM (exterior distance from tube to seat tube)

! Please refer to the Batec Compatibility Chart to ensure your wheelchair model is compatible, and to check the maximum and minimum measurements allowed

USER DETAILS

User name		
User height		cm
User weight		kg ! Maximum accepted weight 110 kg
1	Knee height	CM (distance from floor – upper edge of knee)
2	Shoulder height	CM (distance from floor – upper edge of shoulder)
3	Length of arms	CM (distance from centre of shoulder – centre of the palm with arm fully extended)
4	Total length	CM (distance from back – tips of toes, with feet as far back as possible for the user)
5	Position of feet	CM (distance from end of seat – end of feet)
6	Width of abdomen	CM (distance from back – abdominal area)



COMMENTS